


- 1: Metal Stud Frame
- 2: ArmorWall™ VP (R10, R15, or R21 Standard)
- 3: #14-13 DP1 Self Tapping Screw
- 4: Approved STPE at Seams and Fasteners
- 5: Wall Bracket
- 6: #10-9 Gimlet Point Self Tapping Screw
- 7: Cladding System Channel Backer Plate
- 8: Cladding System Channel
- 9: Ceramic Wall Panel



704-636-2411
www.maxlifeindustries.com

Mail To:
MaxLife Industries
P.O. Box 2128
Salisbury, NC 28145

MAXLIFE
INDUSTRIES
INNOVATING THE
BUILDING ENCLOSURE

Ship To:
1225 Chuck Taylor Lane
Salisbury, North Carolina 28147

DETAIL:
CERAMIC WALL CLADDING ON ARMORWALL™ VP TO METAL STUD
FRAME ASSEMBLY

SCALE:
NTS

REVISION:
01

NOTES:
- FOLLOW ALL CERAMIC WALL SYSTEM MANUFACTURER INSTALLATION FASTENING GUIDELINES.