



- 1: Metal Stud Frame
- 2: ArmorWall VP (R10, R15, or R21 Standard)
- 3: #14-13 Self Tapping Screw
- 4: ArmorSeal Sealant (Gunnable Grade) at all Seams and Fasteners
- 5: Cladding System Clip Attached with #10-9 Gimlet Point Self Tapping Screw
- 6: Cladding Vertical Rail Mounting System
- 7: Ceramic Wall Panel



1-844-MAX4YOU
 (1-844-629-4968)
www.maxlifeindustries.com

Mail To:
 MaxLife Industries
 P.O. Box 2128
 Salisbury, NC 28145

MAXLIFE
 INDUSTRIES
 INNOVATING THE
 BUILDING ENCLOSURE

Ship To:
 4995 South Main Street
 Salisbury, North Carolina 28147

DETAIL TITLE:
 CERAMIC PANEL CLADDING ON ARMORWALL VP TO
 METAL STUD WALL FIELD OF WALL

DETAIL NO.:

SCALE:
 NTS

REVISION:
 01

NOTES:
 - ALWAYS FOLLOW CERAMIC WALL PANEL SYSTEM MANUFACTURER INSTALLATION GUIDELINES.